

Model KT 53 | Cooling incubators with Peltier technology

The KT series combines outstanding performance with impressive energy efficiency and environmental friendliness. The cooled incubators of the KT series are state-of-the-art in application and protect the samples.

BENEFITS

- Safe and reproducible incubation conditions even at high environmental conditions
- Hot air disinfection at 100 °C
- Energy efficient, environmentally friendly and secure



Model 53



Model 115

MAIN FEATURES

- Temperature range: +4 °C to +100 °C
- APT.line™ preheating chamber technology
- Adjustable fan speed
- Electric cooling with Peltier module
- Controller with time-segment and real-time programming
- Display via LCD monitor
- Input via pushbutton/rotary knob
- Inner door made of tempered safety glass
- 2 stainless steel racks
- Stackable
- Class 3.1 independent temperature safety device (DIN 12880) with visual and audible temperature alarm
- Computer interface: Ethernet
- Data recording and USB interface

ORDERING INFORMATION

| Interior volume [L] | Voltage | Option model | Version | Art.-No. |
|---------------------|----------------------------|--------------|--------------|-----------|
| 53 | 200...240 V 1~ ph 50/60 Hz | Standard | KT053-230V | 9020-0311 |
| | 100...120 V 1~ ph 50/60 Hz | Standard | KT053UL-120V | 9020-0312 |

TECHNICAL DATA


| Description | KT053-230V ¹ | KT053UL-120V ¹ |
|---|-------------------------|---------------------------|
| Article Number | 9020-0311 | 9020-0312 |
| Performance Data Temperature | | |
| Temperature range | 4...100 | 4...100 |
| Temperature variation at 37 °C [± K] | 0.3 | 0.3 |
| Temperature fluctuation [± K] | 0.1 | 0.1 |
| Max. heat compensation at 37 °C [W] | 100 | 100 |
| Recovery time after 30 seconds door open at 37 °C [min] | 2 | 2 |

¹ All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

| Description | KT053-230V ¹ | KT053UL-120V ¹ |
|--|-------------------------|---------------------------|
| Article Number | 9020-0311 | 9020-0312 |
| Electrical data | | |
| Rated Voltage [V] | 200...240 | 100...120 |
| Power frequency [Hz] | 50/60 | 50/60 |
| Nominal power [kW] | 0.4 | 0.4 |
| Unit fuse [A] | 10 | 10 |
| Phase (Nominal voltage) | 1~ | 1~ |
| Measures | | |
| Interior volume [L] | 53 | 53 |
| Net weight of the unit (empty) [kg] | 63 | 63 |
| Permitted load [kg] | 40 | 40 |
| Load per rack [kg] | 15 | 15 |
| Wall clearance back [mm] | 100 | 100 |
| Wall clearance sidewise [mm] | 240 | 240 |
| Internal Dimensions | | |
| Width [mm] | 400 | 400 |
| Height [mm] | 400 | 400 |
| Depth [mm] | 334 | 334 |
| Doors | | |
| Inner doors | 1 | 1 |
| Unit doors | 1 | 1 |
| Housing dimensions not incl. fittings and connections | | |
| Width net [mm] | 660 | 660 |
| Height net [mm] | 635 | 635 |
| Depth net [mm] | 630 | 630 |
| Environment-specific data | | |
| Energy consumption at 25 °C [Wh/h] | 75 | 75 |
| Energy consumption at 37 °C [Wh/h] | 75 | 75 |
| Sound-pressure level [dB(A)] | 48 | 48 |
| Fixtures | | |
| Number of shelves (std./max.) | 2/5 | 2/5 |

1 All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS incl. fittings and connections [mm]



OPTIONS

| Designation | Description | * | Art.-No. |
|---|--|-----------|-----------|
| Access port with silicone plug | left | | |
| | 10 mm | 01 | 8012-1290 |
| | 30 mm | 01 | 8012-1158 |
| | 50 mm | 01 | 8012-1165 |
| | right | | |
| | 10 mm | 01 | 8012-1289 |
| | 30 mm | 01 | 8012-1155 |
| | 50 mm | 01 | 8012-1163 |
| | top | | |
| | 10 mm | 01 | 8012-1288 |
| | 30 mm | 01 | 8012-1152 |
| | 50 mm | 01 | 8012-1161 |
| 100 mm | 01 | 8012-1168 | |
| Alarm output, zero-voltage | for temperature (± 2 °C), accessible via 6-pin DIN socket (max. 24 V - 2.5 A), with audible signal that can be switched off | - | 8012-0982 |
| Calibration certificate, expanded | for temperature; for extending the measurement in center of chamber to include another test temperature | - | 8012-1122 |
| Calibration certificate, temperature | for temperature, measurement in center of chamber at specified temperature | - | 8012-1141 |
| | temperature measurement incl. certificate and 27 measuring points at specified temperature | - | 8012-1600 |
| | temperature measurement incl. certificate, 15- 18 measuring points at specified temperature | - | 8012-1579 |
| | temperature measurement incl. certificate, 9 measuring points at specified temperature | - | 8012-1558 |
| Door lock | lockable door handle | - | 8012-1668 |
| Pt 100 temperature sensor | additional flexible Pt 100, interior, for displaying the temperature on the unit display | - | 8012-0935 |
| Shelf, reinforced | positioned at bottom level, max. load 45 kg, with additional attachment for operation of shaking device, stirring device or roller bottle system | - | 8012-0818 |

* Notes › See last page

ACCESSORIES

| Designation | Description | * | Art.-No. |
|--|---|---|-----------|
| APT-COM™ 4 BASIC-Edition | for simple logging and documentation requirements with up to 5 networked units. version 4, BASIC edition | - | 9053-0039 |
| APT-COM™ 4 GLP-Edition | for working under GLP-compliant conditions. Measured values are documented in a tamper-proof way in line with the requirements of FDA Regulation 21 CFR 11. version 4, GLP edition | - | 9053-0042 |
| APT-COM™ 4 PROFESSIONAL-Edition | convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units. version 4, PROFESSIONAL edition | - | 9053-0040 |
| LED light bars | Basic set consisting of 2 pieces, attachment material, control unit for max. 4 light strips, 100-240 V, 50/60 Hz Basic set 300, length 30 cm | - | 8012-1107 |
| | Expansion set consisting of 2 pieces, attachment material: clips. For expanding the basic set of light bars Expansion set 300, length 30 cm | - | 8012-1716 |
| | | - | |
| pH-neutral detergent | concentrated, for gentle remove of residual contaminants; 1 kg | - | 1002-0016 |

* Notes › See last page

| Designation | Description | * | Art.-No. |
|--------------------------------|---|---|-----------|
| Qualification documents | IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit | | |
| | Digital in PDF format | – | 7057-0001 |
| | Hard copy inside folder | – | 7007-0001 |
| | IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO ₂ , O ₂ – or pressure, depending on unit | | |
| | Digital in PDF format | – | 7057-0005 |
| | Hard copy inside folder | – | 7007-0005 |
| Rack | stainless steel | – | 8012-2047 |
| Rack accessories | fasteners (1 set of 4) for additional security of racks | – | 8012-0620 |
| Rack, reinforced | stainless steel, with fasteners (1 set of 4) | – | 8012-0829 |
| Rubber pads | set anti-slip feet | – | 8012-2030 |
| Shelf, perforated | Stainless steel | – | 8012-2083 |
| Table on castors | stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm | – | 9051-0018 |

* Notes › See last page

SERVICES

| Designation | Description | * | Art.-No. |
|--|---|------------|-----------|
| Installation services | | | |
| Unit commissioning | Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work) | 05 | DL10-0100 |
| Unit instructions | Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming | 05 | DL10-0500 |
| Maintenance contracts | | | |
| Maintenance services | | | |
| BRONZE 3-year maintenance contract | Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts | 05 | DL20-0710 |
| GOLD 3-year maintenance contract | Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate | 05 | DL20-0910 |
| Maintenance | One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate | 05 | DL20-0200 |
| SILVER 3-year maintenance contract | Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate | 05 | DL20-0810 |
| Calibration services | | | |
| Calibration certificate, temperature | Calibration of one (1) test temperature specified by the user in center of chamber, including certificate | 03, 04, 05 | DL30-0101 |
| | Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate | 03, 04, 05 | DL30-0102 |
| Temperature measurement, 18 measuring points | Temperature measurement with 18 measuring points with a set value specified by the user, including certificate | 03, 04, 05 | DL30-0118 |
| Temperature measurement, 27 measuring points | Temperature measurement with 27 measuring points with a set value specified by the user, including certificate | 03, 04, 05 | DL30-0127 |
| Temperature measurement, 9 measuring points | Temperature measurement with 9 measuring points with a set value specified by the user, including certificate | 03, 04, 05 | DL30-0109 |
| Validation services | | | |
| Execution of IQ/OQ | Execution of IQ/OQ in accordance with qualification folder | 05 | DL41-0200 |
| Execution of IQ/OQ/PQ | Execution of IQ/OQ/PQ in accordance with qualification folder | 05 | DL44-0500 |
| Warranty service | | | |
| 1-year warranty extension | The warranty is extended by 1 year from the delivery date, wear parts are excluded | – | DL50-0010 |

* Notes › See last page

NOTES

- 01 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- 03 Sensor calibration is performed in an accredited calibration laboratory.
- 04 Calibration is performed according to the BINDER factory standard.
- 05 Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany
TEL +49 7462 2005 0
FAX +49 7462 2005 100
info@binder-world.com
www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China
TEL +852 39070500
FAX +852 39070507
asia@binder-world.com
www.binder-world.com

Representative Office for CIS

Moscow, Russia
TEL +7 495 988 15 16
FAX +7 495 988 15 17
russia@binder-world.com
www.binder-world.com

**BINDER Environmental Testing
Equipment (Shanghai) Co., Ltd.**

Shanghai, P.R. China
TEL +86 21 685 808 25
FAX +86 21 685 808 29
china@binder-world.com
www.binder-world.com

BINDER Inc.

Bohemia, NY, USA
TEL +1 631 224 4340
FAX +1 631 224 4354
usa@binder-world.com
www.binder-world.us